

BeMicron®

Intuitive

Donned without touching the outside of the coverall

Safety

Remove any risk of contamination during the gowning procedure

Economical

Reduce your costs whilst increasing your productivity and quality

Sustainable

All products are reusable



AVAILABLE WITH INTEGRATED MASK

BeMicron Basic

An aseptic one-piece coverall, with or without an integrated mask.

30 sec ESD Grades C ISO 6 → 7

BeMicron Basic can be used in Grade C or ISO 6-7 classes.

Made from an affordable fabric carefully selected for its cost, quality, performance and lasting reliability, it offers excellent mechanical strength and protects against contamination. It has a smooth technical filtering wall, at both front and back, and constitutes a veritable barrier against human contamination.

Thanks to the BeMicron® folding system and donning procedure, the operator's movements follow each other automatically without need to touch the outside of the coverall and without errors in procedure.

✓ Lasts 125+ wash cycles

✓ Strong tear resistance

✓ Sterilization compatible

The donning procedure



1

Out of the bag



2

White = left
Red = right



3

Easy gowning system



4

Easily adjustable



5

Zipper quickly closed

30 sec

BeMicron®
Innovative
cleanroom solutions

www.bemicon.com



in @bemicon
f @bemicon.be
/bemicon

BeMicron®

Intuitive

Donned without touching the outside of the coverall

Safety

Remove any risk of contamination during the gowning procedure

Economical

Reduce your costs whilst increasing your productivity and quality

Sustainable

All products are reusable



A HOOD THAT FITS PERFECTLY

Adjustable both vertically and horizontally with studs, the hood completely encloses the head, providing full protection with excellent comfort.



DURABLE AND EFFECTIVE CUFF

The cuff or stud finish allows the sleeves to fit perfectly into gloves. The cuff is made of antistatic polyester and is resistant to various sterilization processes. The studs are made of stainless steel.



PROTECTIVE CLOTHING WITH OPTIMUM COMFORT

The elastic in the back ensures the BeMicron adjusts perfectly to the body to prevent any «blow-up effect» caused by movements in the body.



BOOTS FIXED TO THE LEGS OF THE COVERALL

Studs on the coverall's leg allow boots to be fixed in a fully protective way. We also supply boots with anti-slip soles which are resistant to the various sterilization cycles and have antistatic qualities.



GOWNING WITHOUT TOUCHING THE COVERALL

The BeMicron is unique in the fact that the outside of the garment is protected from any risk of contact contamination (hand and surface). The base of the zip is already engaged and in place reducing contact time. Simply use the grip to close the zip. Also available with long strap to stamp on and close the zip.



ALSO AVAILABLE WITH INTEGRATED MASK

Hood with a comfortable mask, filtering yet breathable, perfectly covering the nose. The fabric area making up the mask is reduced to fit better around the mouth and nose. This makes the hood more adapted to the shape of the face and extra comfortable.

